

Catalog Number: LTBUS05Y-B
Product ID: 7TAA012LFOR0035
UPC Number: 78621011262
EAN Number: 05415022393408
Status: Active



Liquid Tight Flexible Metallic Conduit, Galvanised Steel Core with PVC Jacket, Conduit Size 1-1/4 Inch, Length 15 Meters/50 Feet, Special Purpose Use, UL 360, CSA, Compliant to RoHS, Working Temperature -20 to 60 Degrees C, Yellow

Representative

North American Specifications (UNSPSC)

| | |
|------------------|--|
| UNSPSC | 39131706 Electrical conduit |
| IGCC | 5543 Liquid Tight Conduit |
| Brand Name | T&B Conduit |
| Type | Liquid Tight Flexible Metallic Conduit |
| Standard | UL 360, CSA, RoHS |
| Trade Size | 1-1/4 Inch/40mm |
| Outside Diameter | 1.660 Inch |
| Inside Diameter | 1.380 Inch |
| Length | 50 ft ; 15 m |
| Material | Galvanized Steel Core |
| Finish | PVC Jacket |
| Color | Yellow |

European Specifications (ETIM)

| | |
|--------------------------------|-----------------------------------|
| ETIM | EC001179 Protective metallic hose |
| Nominal diameter | 40mm |
| Nominal size in inch | 1 1/4 inch |
| Outer diameter | 42.16mm |
| Inner diameter | 35.05mm |
| Material | Steel |
| Surface protection | Other |
| Sheathing material 1st coating | PVC |
| Operating temperature | -20-+60°C |
| Colour | Other |
| Bending strength | Flexible |

Packaging

| | |
|---------------------------|-----------------|
| Outer Quantity | 50 |
| Outer Dimensions (inches) | 25.25x24.5x8.25 |
| Weight Uom | 1.02 lbs. Each |

Documents / Support Tools

| | |
|---------------------------------------|----------------------|
| Technical Drawing / Data Sheet | TDS000009 |
| Technical Drawing / Data Sheet | TDS000117 |
| Technical Drawing / Data Sheet Canada | TDS000009 |
| Catalog US | Available on Website |