

Catalog Number: LTBUS06N-B
Product ID: 7TAA012LFOR0054
UPC Number: 78621011316
EAN Number: 05415022393590
Status: Active



Liquid Tight Flexible Metallic Conduit, Galvanised Steel Core with PVC Jacket, Conduit Size 1-1/2 Inch, Length 15 Meters/50 Feet, Special Purpose Use, UL 360, CSA, Compliant to RoHS, Working Temperature -20 to 60 Degrees C, Green

Representative

North American Specifications (UNSPSC)

UNSPSC	39131706 Electrical conduit
IGCC	5543 Liquid Tight Conduit
Brand Name	T&B Conduit
Type	Liquid Tight Flexible Metallic Conduit
Standard	UL 360, CSA, RoHS
Trade Size	1-1/2 Inch/50mm
Outside Diameter	1.900 Inch
Inside Diameter	1.575 Inch
Length	50 ft ; 15 m
Material	Galvanized Steel Core
Finish	PVC Jacket
Color	Green

European Specifications (ETIM)

ETIM	EC001179 Protective metallic hose
Nominal diameter	50mm
Nominal size in inch	1 1/2 inch
Outer diameter	48.26mm
Inner diameter	40.01mm
Material	Steel
Surface protection	Other
Sheathing material 1st coating	PVC
Operating temperature	-20-+60°C
Colour	Green
Bending strength	Flexible

Packaging

Outer Quantity	50
Outer Dimensions (inches)	33.62x37x10.38
Weight Uom	1.04 lbs. Each

Documents / Support Tools

Technical Drawing / Data Sheet	TDS000009
Technical Drawing / Data Sheet	TDS000117
Technical Drawing / Data Sheet Canada	TDS000009
Catalog US	Available on Website