



**Catalog Number:** LTBUS07N-B  
**Product ID:** 7TAA012LFOR0055  
**UPC Number:** 78621011317  
**EAN Number:** 05415022393606  
**Status:** A



Liquid Tight Flexible Metallic Conduit, Galvanised Steel Core with PVC Jacket, Conduit Size 2 Inch, Length 15 Meters/50 Feet, Special Purpose Use, UL 360, CSA, Compliant to RoHS, Working Temperature -20 to 60 Degrees C, Green

Representative

**North American Specifications (UNSPSC)**

UNSPSC	39131706 Electrical conduit
IGCC	5543 Liquid Tight Conduit
Type	Liquid Tight Flexible Metallic Conduit
Standard	UL 360, CSA, RoHS
Trade Size	2 in ; 63 mm
Outside Diameter	2.375 in
Inside Diameter	2.020 in
Length	50 ft ; 15 m
Material	Galvanized Steel Core
Finish	PVC Jacket
Color	Green

**European Specifications (ETIM)**

ETIM	EC001179 Protective metallic hose
Nominal diameter	63mm
Nominal size in inch	2 inch
Outer diameter	60.33mm
Inner diameter	51.31mm
Material	Steel
Surface protection	Other
Sheathing material 1st coating	PVC
Operating temperature	-20-+60°C
Colour	Green
Bending strength	Flexible

**Packaging**

Outer Quantity	50
Outer Dimensions (inches)	33.62x37x10.38
Weight Uom	1.45 lbs. Each

**Documents / Support Tools**

Technical Drawing / Data Sheet	TDS000009
Technical Drawing / Data Sheet	TDS000117
Catalog US	Available on Website