



**Catalog Number:** LTBUS08Y-A  
**Product ID:** 7TAA012LFOR0038  
**UPC Number:** 78621011267  
**EAN Number:** 05415022393439  
**Status:** A



Liquid Tight Flexible Metallic Conduit, Galvanised Steel Core with PVC Jacket, Conduit Size 2-1/2 Inch, Length 8 Meters/25 Feet, Special Purpose Use, UL 360, CSA, Compliant to RoHS, Working Temperature -20 to 60 Degrees C, Yellow

Representative

#### North American Specifications (UNSPSC)

UNSPSC	39131706 Electrical conduit
IGCC	5543 Liquid Tight Conduit
Type	Liquid Tight Flexible Metallic Conduit
Standard	UL 360, CSA, RoHS
Trade Size	2-1/2 in ; 70 mm
Outside Diameter	2.875 in
Inside Diameter	2.480 in
Length	25 ft ; 8 m
Material	Galvanized Steel Core
Finish	PVC Jacket
Color	Yellow

#### European Specifications (ETIM)

ETIM	EC001179 Protective metallic hose
Nominal diameter	70mm
Nominal size in inch	2 1/2 inch
Outer diameter	73.03mm
Inner diameter	62.99mm
Material	Steel
Surface protection	Other
Sheathing material 1st coating	PVC
Operating temperature	-20-+60°C
Colour	Other
Bending strength	Flexible

#### Packaging

Outer Quantity	25
Outer Dimensions (inches)	33.62x37x10.38
Weight Uom	1.92 lbs. Each

#### Documents / Support Tools

Technical Drawing / Data Sheet	TDS000009
Technical Drawing / Data Sheet	TDS000117
Catalog US	Available on Website