

**Catalog Number:** LTBUS11Y-A  
**Product ID:** 7TAA012LFOR0040  
**UPC Number:** 78621011271  
**EAN Number:** 05415022393453  
**Status:** Active



Liquid Tight Flexible Metallic Conduit, Galvanised Steel Core with PVC Jacket, Conduit Size 4 Inch, Length 8 Meters/25 Feet, Special Purpose Use, UL 360, CSA, Compliant to RoHS, Working Temperature -20 to 60 Degrees C, Yellow

Representative

### North American Specifications (UNSPSC)

UNSPSC	39131706 Electrical conduit
IGCC	5543 Liquid Tight Conduit
Brand Name	T&B Conduit
Type	Liquid Tight Flexible Metallic Conduit
Standard	UL 360, CSA, RoHS
Trade Size	4 Inch/100mm
Outside Diameter	4.500 Inches
Inside Diameter	4.000 Inches
Length	25 ft ; 8 m
Material	Galvanized Steel Core
Finish	PVC Jacket
Color	Yellow

### European Specifications (ETIM)

ETIM	EC001179 Protective metallic hose
Nominal diameter	100mm
Nominal size in inch	4 inch
Outer diameter	114.30mm
Inner diameter	101.60mm
Material	Steel
Surface protection	Other
Sheathing material 1st coating	PVC
Operating temperature	-20-+60°C
Colour	Other
Bending strength	Flexible

### Packaging

Outer Quantity	25
Outer Dimensions (inches)	6.5x60.25x60.25
Weight Uom	3.4 lbs. Each

### Documents / Support Tools

Technical Drawing / Data Sheet	TDS000009
Technical Drawing / Data Sheet	TDS000117
Technical Drawing / Data Sheet Canada	TDS000009
Catalog US	Available on Website