



Catalog Number: LTC050GY
Product ID: 7TAD012610R0006
UPC Number: 78621088076
EAN Number: 05414363155102
Status: A



Actual

Commercial Grade, Type B Liquidtight Flexible PVC Conduit, 1/2 Inch Conduit Size, Approved for Outdoor and Direct Burial in the US, UL Temperature Ratings - 80 Degrees C Dry, 60 Degree C Wet, 70 Degree C Oil, Oil Resistant, Voltage Rating 600V, Gray

- Fast installation, even in tight or cramped spaces.
- Smooth inner diameter allows easy wire pulling.
- Smooth outer jacket uses material approved for outdoor use, is sunlight resistant and oil resistant.
- Lightweight and liquidtight.
- UL Listed for direct burial

North American Specifications (UNSPSC)

| | |
|------------------|---|
| UNSPSC | 39131706 Electrical conduit |
| IGCC | 5535 Electrical conduit |
| Type | Liquidtight Flexible Non-Metallic Conduit |
| Special Features | The Smooth Inner Surface Ensures that Cables and Conductors Can Be Fed Through Very Easily |
| Application | Machine Tools, Motor Hookups, Food Processing Equipment, Extensions from Wire Ways, and Sensor and Micro Switch Wiring Found In Control Consoles. |
| Standard | UL E95745, CSA |
| Trade Size | 1/2 in |
| Outside Diameter | 21.3 mm |
| Inside Diameter | 15.8 mm |
| Length | 30.5 m |
| Voltage Rating | 600 V |
| Material | PVC |
| Color | Gray |

European Specifications (ETIM)

| | |
|---------------------------|----------------------------------|
| ETIM | EC001177 Protective plastic hose |
| Nominal size in inch | 1/2 inch |
| Material | PVC |
| Operating temperature | -18-+105°C |
| Flexibility | Flexible |
| Colour | Grey |
| Approved according to CSA | Y |

Packaging

| | |
|---------------------------|--------------------|
| Outer Quantity | 100 |
| Outer Dimensions (inches) | 19.1x7.5x19.7 |
| Weight Uom | 14.31 lbs. per 100 |

Documents / Support Tools

| | |
|--------------------------------|-----------|
| Technical Drawing / Data Sheet | TDS000138 |
|--------------------------------|-----------|

