



**Catalog Number:** LTC075-2  
**Product ID:** 7TAD012640R0006  
**UPC Number:** 78621070086  
**EAN Number:** 00786210700861  
**Status:** A



Representative

Industrial Grade, Type B Liquidtight Flexible PVC Conduit, 3/4 Inch Conduit Size, Approved for Direct Burial in the US, UL Temperature Ratings - 105 Degrees C Dry, 60 Degree C Wet, 70 Degree C Oil, CSA Temperature Rating 18 to 75 Degrees C, Oil Resistant, Voltage Rating 600V, Blue with Black Markings

**North American Specifications (UNSPSC)**

UNSPSC	39131706 Electrical conduit
IGCC	5535 Electrical conduit
Type	Liquidtight Flexible Non-Metallic Conduit
Special Features	The Smooth Inner Surface Ensures that Cables and Conductors Can Be Fed Through Very Easily
Application	Machine Tools, Motor Hookups, Food Processing Equipment, Extensions from Wire Ways, and Sensor and Micro Switch Wiring Found In Control Consoles.
Standard	UL E95745, CSA
Trade Size	3/4 in
Outside Diameter	26.7 mm
Inside Diameter	20.8 mm
Length	30.5 m
Voltage Rating	600 V
Material	PVC
Color	Blue

**European Specifications (ETIM)**

ETIM	EC001177 Protective plastic hose
Nominal size in inch	3/4 inch
Material	PVC
Operating temperature	-18-+105°C
Flexibility	Flexible
Colour	Blue
Approved according to CSA	Y

**Packaging**

Outer Quantity	100
Outer Dimensions (inches)	22x22x6.5
Weight Uom	19.31 lbs. per 100

**Documents / Support Tools**

Technical Drawing / Data Sheet	TDS000138
--------------------------------	-----------