



**Catalog Number:** LTC075-500  
**Product ID:** 7TAD012620R0006  
**UPC Number:** 78621032384  
**Status:** A



Actual

Industrial Grade, Type B Liquidtight Flexible PVC Conduit, 3/4 Inch Conduit Size, Approved for Outdoor and Direct Burial in the US, UL Temperature Ratings - 105 Degrees C Dry, 60 Degree C Wet, 70 Degree C Oil, CSA Temperature Rating 18 to 75 Degrees C, Oil Resistant, Voltage Rating 600V, Black with Orange Markings, 500 Foot Reel

- Fast installation, even in tight or cramped spaces.
- Smooth inner diameter allows easy wire pulling.
- Smooth outer jacket uses material approved for outdoor use, is sunlight resistant and oil resistant.
- Lightweight and liquidtight.
- UL Listed for direct burial



Actual

**North American Specifications (UNSPSC)**

UNSPSC	39131706 Electrical conduit
IGCC	5535 Electrical conduit
Type	Liquidtight Flexible Non-Metallic Conduit
Special Features	The Smooth Inner Surface Ensures that Cables and Conductors Can Be Fed Through Very Easily
Application	Machine Tools, Motor Hookups, Food Processing Equipment, Extensions from Wire Ways, and Sensor and Micro Switch Wiring Found In Control Consoles.
Standard	UL E95745, CSA
Trade Size	3/4 in
Outside Diameter	26.7 mm
Inside Diameter	20.8 mm
Length	500 ft
Voltage Rating	600 V
Material	PVC
Color	Black

**European Specifications (ETIM)**

ETIM	EC001177 Protective plastic hose
Nominal size in inch	3/4 inch
Material	PVC
Operating temperature	-18-+105°C
Flexibility	Flexible
Colour	Black
Approved according to CSA	Y

**Packaging**

Outer Quantity	500
Outer Dimensions (inches)	30x10x18
Weight Uom	22 lbs. per 100

**Documents / Support Tools**

Technical Drawing / Data Sheet	TDS000138
--------------------------------	-----------

