



**Catalog Number:** LTCES01B-K  
**Product ID:** 7TAA012LM0R0007  
**UPC Number:** 78621011589  
**EAN Number:** 05415022394443  
**Status:** A



Representative

Liquid Tight Flexible Metallic Conduit, Bronze Core with Tin Copper Braid and PVC Jacket, Conduit Size 3/8 Inch, Length 150 Meters/500 Feet, EMC High Performance, Compliant to RoHS and WEEE, Working Temperature -55 to 105 Degrees C, Black

#### North American Specifications (UNSPSC)

UNSPSC	39131706 Electrical conduit
IGCC	5543 Liquid Tight Conduit
Type	Liquid Tight Flexible Metallic Conduit
Standard	RoHS, WEEE
Trade Size	3/8 in ; 16 mm
Outside Diameter	0.710 in
Inside Diameter	0.484 in
Length	500 ft ; 150 m
Material	Bronze Core with Tin Copper Braid
Finish	PVC Jacket
Color	Black

#### European Specifications (ETIM)

ETIM	EC001179 Protective metallic hose
Nominal diameter	16mm
Nominal size in inch	3/8 inch
Outer diameter	18.03mm
Inner diameter	12.29mm
Material	Other
Surface protection	Untreated
Sheathing material 1st coating	Copper, tinned
Sheathing material 2nd coating (exterior)	PVC
Operating temperature	-55-+105°C
Colour	Black
Bending strength	Flexible

#### Packaging

Outer Quantity	500
Outer Dimensions (inches)	20x32x32
Weight Uom	0.3 lbs. Each

#### Documents / Support Tools

Technical Drawing / Data Sheet	TDS000117
Catalog US	Available on Website