



**Catalog Number:** LTCES03B-C  
**Product ID:** 7TAA012LM0R0002  
**UPC Number:** 78621011584  
**EAN Number:** 05415022394399  
**Status:** A



Liquid Tight Flexible Metallic Conduit, Bronze Core with Tin Copper Braid and PVC Jacket, Conduit Size 3/4 Inch, Length 30 Meters/100 Feet, EMC High Performance, Compliant to RoHS and WEEE, Working Temperature -55 to 105 Degrees C, Black

Actual

#### North American Specifications (UNSPSC)

UNSPSC	39131706 Electrical conduit
IGCC	5543 Liquid Tight Conduit
Type	Liquid Tight Flexible Metallic Conduit
Standard	RoHS, WEEE
Trade Size	3/4 in ; 25 mm
Outside Diameter	1.050 in
Inside Diameter	0.820 in
Length	100 ft ; 30 m
Material	Bronze Core with Tin Copper Braid
Finish	PVC Jacket
Color	Black

#### European Specifications (ETIM)

ETIM	EC001179 Protective metallic hose
Nominal diameter	25mm
Nominal size in inch	3/4 inch
Outer diameter	26.67mm
Inner diameter	20.83mm
Material	Other
Surface protection	Untreated
Sheathing material 1st coating	Copper, tinned
Sheathing material 2nd coating (exterior)	PVC
Operating temperature	-55-+105°C
Colour	Black
Bending strength	Flexible

#### Packaging

Outer Quantity	100
Outer Dimensions (inches)	25.25x24.5x8.25
Weight Uom	0.48 lbs. Each

#### Documents / Support Tools

Technical Drawing / Data Sheet	TDS000117
Catalog US	Available on Website