



Catalog Number: LTCES05B-E
Product ID: 7TAA012LM0R0011
UPC Number: 78621011593
EAN Number: 05415022394481
Status: A



Representative

Liquid Tight Flexible Metallic Conduit, Bronze Core with Tin Copper Braid and PVC Jacket, Conduit Size 1-1/4 Inch, Length 60 Meters/200 Feet, EMC High Performance, Compliant to RoHS and WEEE, Working Temperature -55 to 105 Degrees C, Black

North American Specifications (UNSPSC)

UNSPSC	39131706 Electrical conduit
IGCC	5543 Liquid Tight Conduit
Type	Liquid Tight Flexible Metallic Conduit
Standard	RoHS, WEEE
Trade Size	1-1/4 in ; 40 mm
Outside Diameter	1.660 in
Inside Diameter	1.380 in
Length	200 ft ; 60 m
Material	Bronze Core with Tin Copper Braid
Finish	PVC Jacket
Color	Black

European Specifications (ETIM)

ETIM	EC001179 Protective metallic hose
Nominal diameter	40mm
Nominal size in inch	1 1/4 inch
Outer diameter	42.16mm
Inner diameter	35.05mm
Material	Other
Surface protection	Untreated
Sheathing material 1st coating	Copper, tinned
Sheathing material 2nd coating (exterior)	PVC
Operating temperature	-55-+105°C
Colour	Black
Bending strength	Flexible

Packaging

Outer Quantity	200
Outer Dimensions (inches)	20x42x42
Weight Uom	1.1 lbs. Each

Documents / Support Tools

Technical Drawing / Data Sheet	TDS000117
Catalog US	Available on Website