



Catalog Number: LTCES06B-B
Product ID: 7TAA012LM0R0005
UPC Number: 78621011587
EAN Number: 05415022394429
Status: A



Representative

Liquid Tight Flexible Metallic Conduit, Bronze Core with Tin Copper Braid and PVC Jacket, Conduit Size 1-1/2 Inch, Length 15 Meters/50 Feet, EMC High Performance, Compliant to RoHS and WEEE, Working Temperature -55 to 105 Degrees C, Black

North American Specifications (UNSPSC)

UNSPSC	39131706 Electrical conduit
IGCC	5543 Liquid Tight Conduit
Type	Liquid Tight Flexible Metallic Conduit
Standard	RoHS, WEEE
Trade Size	1-1/2 in ; 50 mm
Outside Diameter	1.900 in
Inside Diameter	1.575 in
Length	50 ft ; 15 m
Material	Bronze Core with Tin Copper Braid
Finish	PVC Jacket
Color	Black

European Specifications (ETIM)

ETIM	EC001179 Protective metallic hose
Nominal diameter	50mm
Nominal size in inch	1 1/2 inch
Outer diameter	48.26mm
Inner diameter	40.01mm
Material	Other
Surface protection	Untreated
Sheathing material 1st coating	Copper, tinned
Sheathing material 2nd coating (exterior)	PVC
Operating temperature	-55-+105°C
Colour	Black
Bending strength	Flexible

Packaging

Outer Quantity	50
Outer Dimensions (inches)	33.62x37x10.38
Weight Uom	1.4 lbs. Each

Documents / Support Tools

Technical Drawing / Data Sheet	TDS000117
Catalog US	Available on Website