



**Catalog Number:** LTEUS01B-L  
**Product ID:** 7TAA012LJ0R0014  
**UPC Number:** 78621011555  
**EAN Number:** 05415022394160  
**Status:** A



Representative

Liquid Tight Flexible Metallic Conduit, Galvanised Steel Core with Tin Copper Braid and PVC Jacket, Conduit Size 3/8 Inch, Length 300 Meters/1,000 Feet, EMC Standard Performance, UL 360, Compliant to RoHS and WEEE, Working Temperature -20 to 60 Degrees C, Black

#### North American Specifications (UNSPSC)

UNSPSC	39131706 Electrical conduit
IGCC	5543 Liquid Tight Conduit
Type	Liquid Tight Flexible Metallic Conduit
Standard	UL 360, RoHS, WEEE
Trade Size	3/8 in ; 16 mm
Outside Diameter	0.710 in
Inside Diameter	0.484 in
Length	1,000 ft ; 300 m
Material	Galvanized Steel Core with Tin Copper Braid
Finish	PVC Jacket
Color	Black

#### European Specifications (ETIM)

ETIM	EC001179 Protective metallic hose
Nominal diameter	16mm
Nominal size in inch	3/8 inch
Outer diameter	18.03mm
Inner diameter	12.29mm
Material	Steel
Surface protection	Other
Sheathing material 1st coating	Copper, tinned
Sheathing material 2nd coating (exterior)	PVC
Operating temperature	-20-+60°C
Colour	Black
Bending strength	Flexible

#### Packaging

Outer Quantity	1000
Outer Dimensions (inches)	20x42x42
Weight Uom	0.34 lbs. Each

#### Documents / Support Tools

Technical Drawing / Data Sheet	TDS000117
Catalog US	Available on Website