



Catalog Number: LTEUS03B-C
Product ID: 7TAA012LJ0R0002
UPC Number: 78621011536
EAN Number: 05415022394047
Status: A



Liquid Tight Flexible Metallic Conduit, Galvanised Steel Core with Tin Copper Braid and PVC Jacket, Conduit Size 3/4 Inch, Length 30 Meters/100 Feet, EMC Standard Performance, UL 360, Compliant to RoHS and WEEE, Working Temperature -20 to 60 Degrees C, Black

Actual

North American Specifications (UNSPSC)

UNSPSC	39131706 Electrical conduit
IGCC	5543 Liquid Tight Conduit
Type	Liquid Tight Flexible Metallic Conduit
Standard	UL 360, RoHS, WEEE
Trade Size	3/4 in ; 25 mm
Outside Diameter	1.050 in
Inside Diameter	0.820 in
Length	100 ft ; 30 m
Material	Galvanized Steel Core with Tin Copper Braid
Finish	PVC Jacket
Color	Black

European Specifications (ETIM)

ETIM	EC001179 Protective metallic hose
Nominal diameter	25mm
Nominal size in inch	3/4 inch
Outer diameter	26.67mm
Inner diameter	20.83mm
Material	Steel
Surface protection	Other
Sheathing material 1st coating	Copper, tinned
Sheathing material 2nd coating (exterior)	PVC
Operating temperature	-20-+60°C
Colour	Black
Bending strength	Flexible

Packaging

Outer Quantity	100
Outer Dimensions (inches)	25.25x24.5x8.25
Weight Uom	0.57 lbs. Each

Documents / Support Tools

Technical Drawing / Data Sheet	TDS000117
Catalog US	Available on Website