



**Catalog Number:** LTEUS05B-B  
**Product ID:** 7TAA012LJ0R0004  
**UPC Number:** 78621011538  
**EAN Number:** 05415022394061  
**Status:** A



Representative

Liquid Tight Flexible Metallic Conduit, Galvanised Steel Core with Tin Copper Braid and PVC Jacket, Conduit Size 1-1/4 Inch, Length 15 Meters/50 Feet, EMC Standard Performance, UL 360, Compliant to RoHS and WEEE, Working Temperature -20 to 60 Degrees C, Black

#### North American Specifications (UNSPSC)

UNSPSC	39131706 Electrical conduit
IGCC	5543 Liquid Tight Conduit
Type	Liquid Tight Flexible Metallic Conduit
Standard	UL 360, RoHS, WEEE
Trade Size	1-1/4 in ; 40 mm
Outside Diameter	1.660 in
Inside Diameter	1.380 in
Length	50 ft ; 15 m
Material	Galvanized Steel Core with Tin Copper Braid
Finish	PVC Jacket
Color	Black

#### European Specifications (ETIM)

ETIM	EC001179 Protective metallic hose
Nominal diameter	40mm
Nominal size in inch	1 1/4 inch
Outer diameter	42.16mm
Inner diameter	35.05mm
Material	Steel
Surface protection	Other
Sheathing material 1st coating	Copper, tinned
Sheathing material 2nd coating (exterior)	PVC
Operating temperature	-20-+60°C
Colour	Black
Bending strength	Flexible

#### Packaging

Outer Quantity	50
Outer Dimensions (inches)	25.25x24.5x8.25
Weight Uom	1.02 lbs. Each

#### Documents / Support Tools

Technical Drawing / Data Sheet	TDS000117
Catalog US	Available on Website