



**Catalog Number:** LTEUS06B-B  
**Product ID:** 7TAA012LJ0R0005  
**UPC Number:** 78621011539  
**EAN Number:** 05415022394078  
**Status:** A



Representative

Liquid Tight Flexible Metallic Conduit, Galvanised Steel Core with Tin Copper Braid and PVC Jacket, Conduit Size 1-1/2 Inch, Length 15 Meters/50 Feet, EMC Standard Performance, UL 360, Compliant to RoHS and WEEE, Working Temperature -20 to 60 Degrees C, Black

**North American Specifications (UNSPSC)**

UNSPSC	39131706 Electrical conduit
IGCC	5543 Liquid Tight Conduit
Type	Liquid Tight Flexible Metallic Conduit
Standard	UL 360, RoHS, WEEE
Trade Size	1-1/2 in ; 50 mm
Outside Diameter	1.900 in
Inside Diameter	1.575 in
Length	50 ft ; 15 m
Material	Galvanized Steel Core with Tin Copper Braid
Finish	PVC Jacket
Color	Black

**European Specifications (ETIM)**

ETIM	EC001179 Protective metallic hose
Nominal diameter	50mm
Nominal size in inch	1 1/2 inch
Outer diameter	48.26mm
Inner diameter	40.01mm
Material	Steel
Surface protection	Other
Sheathing material 1st coating	Copper, tinned
Sheathing material 2nd coating (exterior)	PVC
Operating temperature	-20-+60°C
Colour	Black
Bending strength	Flexible

**Packaging**

Outer Quantity	50
Outer Dimensions (inches)	33.62x37x10.38
Weight Uom	1.24 lbs. Each

**Documents / Support Tools**

Technical Drawing / Data Sheet	TDS000117
Catalog US	Available on Website