

**Catalog Number:** LTFES04W-C  
**Product ID:** 7TAA012LQ0R0003  
**UPC Number:** 78621011609  
**EAN Number:** 05415022446197  
**Status:** Active



Liquid Tight Flexible Metallic Conduit, Food and Beverage Grade, Galvanized Steel Core with PVC Jacket, Conduit Size 1 Inch, Length 30 Meters/100 Feet, Working Temperature -20 to 80 Degrees C, Compliant to RoHS and WEEE, White

Representative

### North American Specifications (UNSPSC)

UNSPSC	39131706 Electrical conduit
IGCC	5543 Liquid Tight Conduit
Brand Name	T&B
Type	Flexible Metal Conduit
Standard	RoHS, WEEE
Trade Size	1 Inch
Outside Diameter	1.315
Inside Diameter	1.041
Length	100 ft
Material	Galvanized Steel Core with PVC Jacket
Color	White

### European Specifications (ETIM)

ETIM	EC001179 Protective metallic hose
Nominal diameter	32mm
Nominal size in inch	1 inch
Material	Steel
Surface protection	Other
Sheathing material 2nd coating (exterior)	PVC
Operating temperature	-20-+80°C
Colour	White
Bending strength	Flexible

### Packaging

Outer Quantity	100
Outer Dimensions (inches)	25.25x24.5x8.25
Weight Uom	0.53 lbs. Each

### Documents / Support Tools

Technical Drawing / Data Sheet	TDS000022
Technical Drawing / Data Sheet	TDS000117
Technical Drawing / Data Sheet Canada	TDS000022
Catalog US	Available on Website