



**Catalog Number:** LTFES07W-B  
**Product ID:** 7TAA012LQ0R0006  
**UPC Number:** 78621011612  
**EAN Number:** 05415022446227  
**Status:** A



Liquid Tight Flexible Metallic Conduit, Food and Beverage Grade, Galvanized Steel Core with PVC Jacket, Conduit Size 2 Inch, Length 15 Meters/50 Feet, Working Temperature -20 to 80 Degrees C, Compliant to RoHS and WEEE, White

Representative

#### North American Specifications (UNSPSC)

UNSPSC	39131706 Electrical conduit
IGCC	5543 Liquid Tight Conduit
Type	Flexible Metal Conduit
Standard	RoHS, WEEE
Trade Size	2 in
Outside Diameter	2.375 in
Inside Diameter	2.02 in
Length	50 ft
Material	Galvanized Steel Core with PVC Jacket
Color	White

#### European Specifications (ETIM)

ETIM	EC001179 Protective metallic hose
Nominal diameter	63mm
Nominal size in inch	2 inch
Material	Steel
Surface protection	Other
Sheathing material 2nd coating (exterior)	PVC
Operating temperature	-20-+80°C
Colour	White
Bending strength	Flexible

#### Packaging

Outer Quantity	50
Outer Dimensions (inches)	33.62x37x10.38
Weight Uom	1.16 lbs. Each

#### Documents / Support Tools

Technical Drawing / Data Sheet	TDS000022
Technical Drawing / Data Sheet	TDS000117
Catalog US	Available on Website