



Catalog Number: LTFUS05W-B
Product ID: 7TAA012LP0R0004
UPC Number: 78621011600
EAN Number: 05415022446104
Status: A



Liquid Tight Flexible Metallic Conduit, Food Grade, Galvanized Steel Core with PVC Jacket, Conduit Size 1-1/4 Inch, Length 15 Meters/50 Feet, Working Temperature -30 to 80 Degrees C, UL 514B, Compliant to RoHS and WEEE, White

Representative

North American Specifications (UNSPSC)

UNSPSC	39131706 Electrical conduit
IGCC	5543 Liquid Tight Conduit
Type	Flexible Metal Conduit
Standard	RoHS, WEEE, cUL, CSA
Trade Size	1-1/4 in
Outside Diameter	1.66 in
Inside Diameter	1.38 in
Length	50 ft
Material	Galvanized Steel Core with PVC Jacket
Color	White

European Specifications (ETIM)

ETIM	EC001179 Protective metallic hose
Nominal diameter	40mm
Nominal size in inch	1 1/4 inch
Material	Steel
Surface protection	Other
Sheathing material 2nd coating (exterior)	PVC
Operating temperature	-30-+80°C
Colour	White
Bending strength	Flexible
Approved according to CSA	Y

Packaging

Outer Quantity	50
Outer Dimensions (inches)	25.25x24.5x8.25
Weight Uom	1.02 lbs. Each

Documents / Support Tools

Technical Drawing / Data Sheet	TDS000021
Technical Drawing / Data Sheet	TDS000117
Catalog US	Available on Website