


Catalog Number: LTGCS11B-A
Product ID: 7TAA012LH0R0009
UPC Number: 78621010780
EAN Number: 05415022391022
Status: Active



Liquid Tight Flexible Metallic Conduit, General Purpose, Galvanised Steel Core with PVC Jacket, Conduit Size 4 Inch, Length 8 Meters/25 Feet, Working Temperature -40 to 75 Degrees C, CSA LR-72635, Compliant to RoHS, Black

General Purpose, CSA Certified Liquid-tight Flexible Metallic Conduits provide excellent strength and liquid-tight performance, meeting CEC requirements

Representative

- Full compliance to IEC 61386 requirements, CE compliant
- Coordinated performance with Ser. 52/53 Steel Fittings
- CSA & IP ingress protection ratings aligned with industrial enclosures
- Smooth extruded jackets provide best performance with fittings
- Ideal for machine and equipment, OEMs, panel builders and industrial, light manufacturing, commercial and outdoor installations
- Liquid tight applications against water, oils, cutting fluids, mild acids
- For use in electrical circuits up to 1,000 volts

North American Specifications (UNSPSC)

UNSPSC	39131706 Electrical conduit
IGCC	5543 Liquid Tight Conduit
Brand Name	T&B Conduit
Type	Liquid Tight Flexible Metallic Conduit
Special Features	Designed to meet CSA C22.2 No. 56 ID/OD dimension requirements
Application	For use to CEC as described in Section 12-1300 for dry damp or wet locations where flexibility is required
Standard	CSA, RoHS
Trade Size	4 Inch
Outside Diameter	4.500 Inches
Inside Diameter	4.000 Inches
Length	25 ft ; 8 m
Radius	610 Millimeters
Material	Galvanised Steel
Finish	PVC Jacket
Color	Black

European Specifications (ETIM)

ETIM	EC001179 Protective metallic hose
Nominal diameter	100mm
Nominal size in inch	4 inch
Outer diameter	114.30mm
Inner diameter	101.60mm
Material	Steel
Surface protection	Untreated
Sheathing material 1st coating	PVC
Operating temperature	-40-+75°C
Degree of protection (IP)	IP67
Weight	5.21kg/m
Colour	Black
Bending strength	Flexible

Approved according to DIN EN 61386-23 Y

With approval according to UL N

Approved according to CSA Y

Packaging

Outer Quantity 25

Outer Dimensions (inches) 12.5x65x65

Weight Uom 4 lbs. Each

Documents / Support Tools

Technical Drawing / Data Sheet TDS000003

Technical Drawing / Data Sheet TDS000117

Technical Drawing / Data Sheet Canada TDS000003

Support/Tools Available on Website

Catalog US Available on Website