



**Catalog Number:** LTGUS06G-D  
**Product ID:** 7TAA012LN0R0025  
**UPC Number:** 78621010919  
**EAN Number:** 05415022391381  
**Status:** A



Liquid Tight Flexible Metallic Conduit, General Purpose, Galvanised Steel Core with PVC Jacket, Conduit Size 1-1/2 Inch, Length 45 Meters/150 Feet, Working Temperature -30 to 80 Degrees C, UL E125517, CSA LR-72635, Compliant to RoHS, Gray

General Purpose, UL Listed Liquid-tight Flexible Metallic Conduits providing premier performance in the toughest applications

Representative

- Coordinated performance with Ser. 52/53 Steel Fittings
- Smooth extruded jackets provide best performance with fittings
- Used extensively in machine tool and other industrial environments where flexibility is necessary for motion, vibration and bending
- Listed and marked for direct burial in earth or in poured concrete
- Liquid-tight applications against water, oils, cutting fluids and mild acids

**North American Specifications (UNSPSC)**

UNSPSC	39131706 Electrical conduit
IGCC	5543 Liquid Tight Conduit
Type	Liquid Tight Flexible Metallic Conduit
Special Features	High quality cores and jackets for excellent strength and durability
Application	General Purpose
Standard	UL E125517, CSA LR-72635, RoHS
Trade Size	1-1/2 in
Outside Diameter	1.900 in
Inside Diameter	1.575 in
Length	150 ft ; 45 m
Radius	114 mm
Material	Galvanised Steel
Finish	PVC Jacket
Color	Gray

**European Specifications (ETIM)**

ETIM	EC001179 Protective metallic hose
Nominal diameter	50mm
Nominal size in inch	1 1/2 inch
Outer diameter	48.26mm
Inner diameter	40.01mm
Material	Steel
Surface protection	Untreated
Sheathing material 1st coating	PVC
Operating temperature	-30-+80°C
Degree of protection (IP)	IP67
Weight	1.84kg/m
Colour	Grey
Bending strength	Flexible
Approved according to DIN EN 61386-23	Y
With approval according to UL	Y
Approved according to CSA	Y

**Packaging**

Outer Quantity	150
----------------	-----



Outer Dimensions (inches)	20x32x32
Weight Uom	1.04 lbs. Each

<b>Documents / Support Tools</b>	
Technical Drawing / Data Sheet	TDS000001
Technical Drawing / Data Sheet	TDS000117
Support/Tools	Available on Website
Catalog US	Available on Website