



Catalog Number: LTMES02G-L
Product ID: 7TAA012LK0R0018
UPC Number: 78621011581
EAN Number: 05415022394368
Status: A



Representative

Liquid Tight Flexible Metallic Conduit, Bronze Core with PVC Jacket, Conduit Size 1/2 Inch, Length 300 Meters/1,000 Feet, EMC Mid Performance, Halogen Free, Compliant to RoHS and WEEE, Working Temperature -55 to 105 Degrees C, Gray

North American Specifications (UNSPSC)

UNSPSC	39131706 Electrical conduit
IGCC	5543 Liquid Tight Conduit
Type	Liquid Tight Flexible Metallic Conduit
Standard	RoHS, WEEE
Trade Size	1/2 in ; 20 mm
Outside Diameter	0.840 in
Inside Diameter	0.622 in
Length	1,000 ft ; 300 m
Material	Bronze Core
Finish	PVC Jacket
Color	Gray

European Specifications (ETIM)

ETIM	EC001179 Protective metallic hose
Nominal diameter	20mm
Nominal size in inch	1/2 inch
Outer diameter	21.34mm
Inner diameter	15.80mm
Material	Other
Surface protection	Untreated
Sheathing material 1st coating	PVC
Operating temperature	-55-+105°C
Colour	Grey
Bending strength	Flexible

Packaging

Outer Quantity	1000
Outer Dimensions (inches)	20x30x30
Weight Uom	0.37 lbs. Each

Documents / Support Tools

Technical Drawing / Data Sheet	TDS000117
--------------------------------	-----------