



Catalog Number: LTMES04G-J
Product ID: 7TAA012LK0R0013
UPC Number: 78621011575
EAN Number: 05415022394313
Status: A



Representative

Liquid Tight Flexible Metallic Conduit, Bronze Core with PVC Jacket, Conduit Size 1 Inch, Length 120 Meters/400 Feet, EMC Mid Performance, Halogen Free, Compliant to RoHS and WEEE, Working Temperature -55 to 105 Degrees C, Gray

North American Specifications (UNSPSC)

UNSPSC	39131706 Electrical conduit
IGCC	5543 Liquid Tight Conduit
Type	Liquid Tight Flexible Metallic Conduit
Standard	RoHS, WEEE
Trade Size	1 in ; 32 mm
Outside Diameter	1.315 in
Inside Diameter	1.041 in
Length	400 ft ; 120 m
Material	Bronze Core
Finish	PVC Jacket
Color	Gray

European Specifications (ETIM)

ETIM	EC001179 Protective metallic hose
Nominal diameter	32mm
Nominal size in inch	1 inch
Outer diameter	33.40mm
Inner diameter	26.44mm
Material	Other
Surface protection	Untreated
Sheathing material 1st coating	PVC
Operating temperature	-55-+105°C
Colour	Grey
Bending strength	Flexible

Packaging

Outer Quantity	400
Outer Dimensions (inches)	20x32x32
Weight Uom	0.85 lbs. Each

Documents / Support Tools

Technical Drawing / Data Sheet	TDS000117
--------------------------------	-----------