



Catalog Number: LTMES07G-B
Product ID: 7TAA012LK0R0006
UPC Number: 78621011564
EAN Number: 05415022394245
Status: A



Liquid Tight Flexible Metallic Conduit, Bronze Core with PVC Jacket, Conduit Size 2 Inch, Length 15 Meters/50 Feet, EMC Mid Performance, Halogen Free, Compliant to RoHS and WEEE, Working Temperature -55 to 105 Degrees C, Gray

Representative

North American Specifications (UNSPSC)

UNSPSC	39131706 Electrical conduit
IGCC	5543 Liquid Tight Conduit
Type	Liquid Tight Flexible Metallic Conduit
Standard	RoHS, WEEE
Trade Size	2 in ; 63 mm
Outside Diameter	2.375 in
Inside Diameter	2.020 in
Length	50 ft ; 15 m
Material	Bronze Core
Finish	PVC Jacket
Color	Gray

European Specifications (ETIM)

ETIM	EC001179 Protective metallic hose
Nominal diameter	63mm
Nominal size in inch	2 inch
Outer diameter	60.33mm
Inner diameter	51.31mm
Material	Other
Surface protection	Untreated
Sheathing material 1st coating	PVC
Operating temperature	-55-+105°C
Colour	Grey
Bending strength	Flexible

Packaging

Outer Quantity	50
Outer Dimensions (inches)	33.62x37x10.38
Weight Uom	1.8 lbs. Each

Documents / Support Tools

Technical Drawing / Data Sheet	TDS000117
--------------------------------	-----------