



**Catalog Number:** LTMES11G-A  
**Product ID:** 7TAA012LK0R0009  
**UPC Number:** 78621011568  
**EAN Number:** 05415022394276  
**Status:** A



Liquid Tight Flexible Metallic Conduit, Bronze Core with PVC Jacket, Conduit Size 4 Inch, Length 8 Meters/25 Feet, EMC Mid Performance, Halogen Free, Compliant to RoHS and WEEE, Working Temperature -55 to 105 Degrees C, Gray

Representative

**North American Specifications (UNSPSC)**

UNSPSC	39131706 Electrical conduit
IGCC	5543 Liquid Tight Conduit
Type	Liquid Tight Flexible Metallic Conduit
Standard	RoHS, WEEE
Trade Size	4 in ; 100 mm
Outside Diameter	4.500 in
Inside Diameter	4.000 in
Length	25 ft ; 8 m
Material	Bronze Core
Finish	PVC Jacket
Color	Gray

**European Specifications (ETIM)**

ETIM	EC001179 Protective metallic hose
Nominal diameter	100mm
Nominal size in inch	4 inch
Outer diameter	114.30mm
Inner diameter	101.60mm
Material	Other
Surface protection	Untreated
Sheathing material 1st coating	PVC
Operating temperature	-55-+105°C
Colour	Grey
Bending strength	Flexible

**Packaging**

Outer Quantity	25
Outer Dimensions (inches)	6.5x60.25x60.25
Weight Uom	3.88 lbs. Each

**Documents / Support Tools**

Technical Drawing / Data Sheet	TDS000117
--------------------------------	-----------