




**Catalog Number:** LTTES09G-P  
**Product ID:** 7TAA012LC0R0020  
**UPC Number:** 78621010627  
**EAN Number:** 05415022390483  
**Status:** A



Liquid Tight Flexible Metallic Conduit, Wide Temperature Range, Galvanised Steel Core with PVC Jacket, Conduit Size 3 Inch, Length 50 Meters/175 Feet, Working Temperature -55 to 105 Degrees C, Intermitting to 120 Degrees C, Compliant to RoHS, Gray

Wide temperature, CE compliant Liquid-tight Flexible Metallic Conduits provide excellent performance in low and high temperatures

Representative

- Coordinated performance with Series 52/53 Steel Fittings
- Ingress protection ratings aligned with industrial enclosures
- Smooth extruded jackets provide best performance with fittings
- Ideal for use in outdoor applications for cold environment
- Liquid tight applications against water, oils, cutting fluids, mild acids

**North American Specifications (UNSPSC)**

UNSPSC	39131706 Electrical conduit
IGCC	5543 Liquid Tight Conduit
Type	Liquid Tight Flexible Metallic Conduit
Special Features	Designed to meet UL 360 ID/OD dimension requirements
Application	Used with high temperature machine tool wiring
Standard	RoHS
Trade Size	3 in
Outside Diameter	3.500 in
Inside Diameter	3.070 in
Length	175 ft ; 50 m
Radius	254 mm
Material	Galvanised Steel
Finish	PVC Jacket
Color	Gray

**European Specifications (ETIM)**

ETIM	EC001179 Protective metallic hose
Nominal diameter	80mm
Nominal size in inch	3 inch
Outer diameter	88.90mm
Inner diameter	77.98mm
Material	Steel
Surface protection	Untreated
Sheathing material 1st coating	PVC
Operating temperature	-55-+105°C
Degree of protection (IP)	IP67
Weight	3.75kg/m
Colour	Grey
Bending strength	Flexible
Approved according to DIN EN 61386-23	Y
With approval according to UL	N
Approved according to CSA	N

**Packaging**

Outer Quantity	175
----------------	-----



Outer Dimensions (inches)	35x58x58
Weight Uom	4.14 lbs. Each

**Documents / Support Tools**

Technical Drawing / Data Sheet	TDS000005
Technical Drawing / Data Sheet	TDS000117
Support/Tools	Available on Website