

Catalog Number: LTXES03B-L
Product ID: 7TAA012LE0R0019
UPC Number: 78621010745
EAN Number: 05415022390926
Status: Active



Liquid Tight Flexible Metallic Conduit, Extreme Temperature Range, Galvanised Steel Core with TPR Jacket, Conduit Size 3/4 Inch, Length 300 Meters/1,000 Feet, Working Temperature -60 to 150 Degrees C, Intermittent to 165 Degrees C, Compliant to RoHS, Black

Extreme temperature, CE compliant Liquid-tight Flexible Metallic Conduits provide excellent performance in extreme low and high temperature environments

Actual

- Coordinated performance with Series 52/53 Steel Fittings
- Ingress protection ratings aligned with industrial enclosures
- Smooth extruded jackets provide best performance with fittings
- Ideal for machine and equipment, OEMs, panel builders and industrial, light manufacturing, commercial and outdoor installations
- Liquid tight applications against water, oils and mild acids
- For use in electrical circuits up to 1,000 volts

North American Specifications (UNSPSC)

UNSPSC	39131706 Electrical conduit
IGCC	5543 Liquid Tight Conduit
Brand Name	T&B Conduit
Type	Liquid Tight Flexible Metallic Conduit
Special Features	Designed to meet UL 360 ID/OD dimension requirements
Application	Used in extremely high temperature applications such as commercial ovens and refrigeration, industrial furnaces and foundries
Standard	RoHS
Trade Size	3/4 Inch
Outside Diameter	1.050 Inch
Inside Diameter	0.820 Inch
Length	1,000 ft ; 300 m
Radius	64 Millimeters
Material	Galvanised Steel
Finish	TPR Jacket
Color	Black

European Specifications (ETIM)

ETIM	EC001179 Protective metallic hose
Nominal diameter	25mm
Nominal size in inch	3/4 inch
Outer diameter	26.67mm
Inner diameter	20.83mm
Material	Steel
Surface protection	Untreated
Sheathing material 1st coating	Megolon, flame retardant
Operating temperature	-60-+150°C
Degree of protection (IP)	IP67
Weight	0.58kg/m
Colour	Black
Bending strength	Flexible
Approved according to DIN EN 61386-23 Y	

With approval according to UL	N
Approved according to CSA	N

Packaging

Outer Quantity	1000
Outer Dimensions (inches)	20x42x42
Weight Uom	0.41 lbs. Each

Documents / Support Tools

Technical Drawing / Data Sheet	TDS000006
Technical Drawing / Data Sheet	TDS000117
Technical Drawing / Data Sheet Canada	TDS000006
Support/Tools	Available on Website
Catalog US	Available on Website