



Catalog Number: LTZES02G-C
Product ID: 7TAA012LG0R0001
UPC Number: 78621011323
EAN Number: 05415022393651
Status: A



Representative

Liquid Tight Flexible Metallic Conduit, Galvanised Steel Core with PVC Jacket, Conduit Size 1/2 Inch, Length 30 Meters/100 Feet, Halogen Free, Compliant to RoHS, Working Temperature -40 to 80 Degrees C, Gray

North American Specifications (UNSPSC)

UNSPSC	39131706 Electrical conduit
IGCC	5543 Liquid Tight Conduit
Type	Liquid Tight Flexible Metallic Conduit
Standard	RoHS
Trade Size	1/2 in ; 20 mm
Outside Diameter	0.840 in
Inside Diameter	0.622 in
Length	100 ft ; 30 m
Material	Galvanized Steel Core
Finish	PVC Jacket
Color	Gray

European Specifications (ETIM)

ETIM	EC001179 Protective metallic hose
Nominal diameter	20mm
Nominal size in inch	1/2 inch
Outer diameter	21.34mm
Inner diameter	15.80mm
Material	Steel
Surface protection	Other
Sheathing material 1st coating	PVC
Operating temperature	-40-+80°C
Colour	Grey
Bending strength	Flexible

Packaging

Outer Quantity	100
Outer Dimensions (inches)	17.62x16.75x8
Weight Uom	0.24 lbs. Each

Documents / Support Tools

Technical Drawing / Data Sheet	TDS000011
Technical Drawing / Data Sheet	TDS000117