



**Catalog Number:** LTZES03G-K  
**Product ID:** 7TAA012LG0R0013  
**UPC Number:** 78621011428  
**EAN Number:** 05415022393774  
**Status:** A



Representative

Liquid Tight Flexible Metallic Conduit, Galvanised Steel Core with PVC Jacket, Conduit Size 3/4 Inch, Length 150 Meters/500 Feet, Halogen Free, Compliant to RoHS, Working Temperature -40 to 80 Degrees C, Gray

#### North American Specifications (UNSPSC)

UNSPSC	39131706 Electrical conduit
IGCC	5543 Liquid Tight Conduit
Type	Liquid Tight Flexible Metallic Conduit
Standard	RoHS
Trade Size	3/4 in ; 25 mm
Outside Diameter	1.050 in
Inside Diameter	0.820 in
Length	500 ft ; 150 m
Material	Galvanized Steel Core
Finish	PVC Jacket
Color	Gray

#### European Specifications (ETIM)

ETIM	EC001179 Protective metallic hose
Nominal diameter	25mm
Nominal size in inch	3/4 inch
Outer diameter	26.67mm
Inner diameter	20.83mm
Material	Steel
Surface protection	Other
Sheathing material 1st coating	PVC
Operating temperature	-40-+80°C
Colour	Grey
Bending strength	Flexible

#### Packaging

Outer Quantity	500
Outer Dimensions (inches)	20x30x30
Weight Uom	0.33 lbs. Each

#### Documents / Support Tools

Technical Drawing / Data Sheet	TDS000011
Technical Drawing / Data Sheet	TDS000117