

Catalog Number: LTZES04G-J
Product ID: 7TAA012LG0R0014
UPC Number: 78621011444
EAN Number: 05415022393781
Status: Active



Representative

Liquid Tight Flexible Metallic Conduit, Galvanised Steel Core with PVC Jacket, Conduit Size 1 Inch, Length 120 Meters/400 Feet, Halogen Free, Compliant to RoHS, Working Temperature -40 to 80 Degrees C, Gray

North American Specifications (UNSPSC)

UNSPSC	39131706 Electrical conduit
IGCC	5543 Liquid Tight Conduit
Brand Name	T&B Conduit
Type	Liquid Tight Flexible Metallic Conduit
Standard	RoHS
Trade Size	1 Inch/32mm
Outside Diameter	1.315 Inch
Inside Diameter	1.041 Inch
Length	400 ft ; 120 m
Material	Galvanized Steel Core
Finish	PVC Jacket
Color	Gray

European Specifications (ETIM)

ETIM	EC001179 Protective metallic hose
Nominal diameter	32mm
Nominal size in inch	1 inch
Outer diameter	33.40mm
Inner diameter	26.44mm
Material	Steel
Surface protection	Other
Sheathing material 1st coating	PVC
Operating temperature	-40-+80°C
Colour	Grey
Bending strength	Flexible

Packaging

Outer Quantity	400
Outer Dimensions (inches)	20x30x30
Weight Uom	0.53 lbs. Each

Documents / Support Tools

Technical Drawing / Data Sheet	TDS000011
Technical Drawing / Data Sheet	TDS000117
Technical Drawing / Data Sheet Canada	TDS000011