



Catalog Number: LTZES05G-B
Product ID: 7TAA012LG0R0004
UPC Number: 78621011347
EAN Number: 05415022393682
Status: A



Representative

Liquid Tight Flexible Metallic Conduit, Galvanised Steel Core with PVC Jacket, Conduit Size 1-1/4 Inch, Length 15 Meters/50 Feet, Halogen Free, Compliant to RoHS, Working Temperature -40 to 80 Degrees C, Gray

North American Specifications (UNSPSC)

UNSPSC	39131706 Electrical conduit
IGCC	5543 Liquid Tight Conduit
Type	Liquid Tight Flexible Metallic Conduit
Standard	RoHS
Trade Size	1-1/4 in ; 40 mm
Outside Diameter	1.660 in
Inside Diameter	1.380 in
Length	50 ft ; 15 m
Material	Galvanized Steel Core
Finish	PVC Jacket
Color	Gray

European Specifications (ETIM)

ETIM	EC001179 Protective metallic hose
Nominal diameter	40mm
Nominal size in inch	1 1/4 inch
Outer diameter	42.16mm
Inner diameter	35.05mm
Material	Steel
Surface protection	Other
Sheathing material 1st coating	PVC
Operating temperature	-40-+80°C
Colour	Grey
Bending strength	Flexible

Packaging

Outer Quantity	50
Outer Dimensions (inches)	25.25x24.5x8.25
Weight Uom	0.68 lbs. Each

Documents / Support Tools

Technical Drawing / Data Sheet	TDS000011
Technical Drawing / Data Sheet	TDS000117