



**Catalog Number:** LTZES06B-D  
**Product ID:** 7TAA012LG0R0035  
**UPC Number:** 78621011528  
**EAN Number:** 05415022393996  
**Status:** A



Representative

Liquid Tight Flexible Metallic Conduit, Galvanised Steel Core with PVC Jacket, Conduit Size 1-1/2 Inch, Length 45 Meters/150 Feet, Halogen Free, Compliant to RoHS, Working Temperature -40 to 80 Degrees C, Black

#### North American Specifications (UNSPSC)

UNSPSC	39131706 Electrical conduit
IGCC	5543 Liquid Tight Conduit
Type	Liquid Tight Flexible Metallic Conduit
Standard	RoHS
Trade Size	1-1/2 in ; 50 mm
Outside Diameter	1.900 in
Inside Diameter	1.575 in
Length	150 ft ; 45 m
Material	Galvanized Steel Core
Finish	PVC Jacket
Color	Black

#### European Specifications (ETIM)

ETIM	EC001179 Protective metallic hose
Nominal diameter	50mm
Nominal size in inch	1 1/2 inch
Outer diameter	48.26mm
Inner diameter	40.01mm
Material	Steel
Surface protection	Other
Sheathing material 1st coating	PVC
Operating temperature	-40-+80°C
Colour	Black
Bending strength	Flexible

#### Packaging

Outer Quantity	150
Outer Dimensions (inches)	20x32x32
Weight Uom	0.88 lbs. Each

#### Documents / Support Tools

Technical Drawing / Data Sheet	TDS000011
Technical Drawing / Data Sheet	TDS000117
Catalog US	Available on Website