

Catalog Number: LTZES07G-C
Product ID: 7TAA012LG0R0017
UPC Number: 78621011474
EAN Number: 05415022393811
Status: Active



Liquid Tight Flexible Metallic Conduit, Galvanised Steel Core with PVC Jacket, Conduit Size 2 Inch, Length 30 Meters/100 Feet, Halogen Free, Compliant to RoHS, Working Temperature -40 to 80 Degrees C, Gray

Representative

North American Specifications (UNSPSC)

UNSPSC	39131706 Electrical conduit
IGCC	5543 Liquid Tight Conduit
Brand Name	T&B Conduit
Type	Liquid Tight Flexible Metallic Conduit
Standard	RoHS
Trade Size	2 Inch/63mm
Outside Diameter	2.375 Inches
Inside Diameter	2.020 Inches
Length	100 ft ; 30 m
Material	Galvanized Steel Core
Finish	PVC Jacket
Color	Gray

European Specifications (ETIM)

ETIM	EC001179 Protective metallic hose
Nominal diameter	63mm
Nominal size in inch	2 inch
Outer diameter	60.33mm
Inner diameter	51.31mm
Material	Steel
Surface protection	Other
Sheathing material 1st coating	PVC
Operating temperature	-40-+80°C
Colour	Grey
Bending strength	Flexible

Packaging

Outer Quantity	100
Outer Dimensions (inches)	20x32x32
Weight Uom	1.16 lbs. Each

Documents / Support Tools

Technical Drawing / Data Sheet	TDS000011
Technical Drawing / Data Sheet	TDS000117
Technical Drawing / Data Sheet Canada	TDS000011