



Catalog Number: LTZUS01B-K
Product ID: 7TAA012LT0R0010
UPC Number: 78621011624
EAN Number: 05415022394610
Status: A



Liquid Tight Flexible Metallic Conduit, Galvanised Steel Core with PVC Jacket, Conduit Size 3/8 Inch, Length 150 Meters/500 Feet, Halogen Free, UL 360, CSA, Compliant to RoHS, Working Temperature -40 to 80 Degrees C, Black

Representative

North American Specifications (UNSPSC)

UNSPSC	39131706 Electrical conduit
IGCC	5543 Liquid Tight Conduit
Type	Liquid Tight Flexible Metallic Conduit
Standard	UL 360, CSA, RoHS
Trade Size	3/8 in ; 16 mm
Outside Diameter	0.710 in
Inside Diameter	0.484 in
Length	500 ft ; 150 m
Material	Galvanized Steel Core
Finish	PVC Jacket
Color	Black

European Specifications (ETIM)

ETIM	EC001179 Protective metallic hose
Nominal diameter	16mm
Nominal size in inch	3/8 inch
Outer diameter	18.03mm
Inner diameter	12.29mm
Material	Steel
Surface protection	Other
Sheathing material 1st coating	PVC
Operating temperature	-40-+80°C
Colour	Black
Bending strength	Flexible

Packaging

Outer Quantity	500
Outer Dimensions (inches)	20x24x24
Weight Uom	0.01 lbs. Each

Documents / Support Tools

Technical Drawing / Data Sheet	TDS000010
Technical Drawing / Data Sheet	TDS000117
Catalog US	Available on Website