



Catalog Number: LTZUS02B-L
Product ID: 7TAA012LT0R0018
UPC Number: 78621011632
EAN Number: 05415022394696
Status: A



Liquid Tight Flexible Metallic Conduit, Galvanised Steel Core with PVC Jacket, Conduit Size 1/2 Inch, Length 300 Meters/1,000 Feet, Halogen Free, UL 360, CSA, Compliant to RoHS, Working Temperature -40 to 80 Degrees C, Black

Representative

North American Specifications (UNSPSC)

UNSPSC	39131706 Electrical conduit
IGCC	5543 Liquid Tight Conduit
Type	Liquid Tight Flexible Metallic Conduit
Standard	UL 360, CSA, RoHS
Trade Size	1/2 in ; 20 mm
Outside Diameter	0.840 in
Inside Diameter	0.622 in
Length	1,000 ft ; 300 m
Material	Galvanized Steel Core
Finish	PVC Jacket
Color	Black

European Specifications (ETIM)

ETIM	EC001179 Protective metallic hose
Nominal diameter	20mm
Nominal size in inch	1/2 inch
Outer diameter	21.34mm
Inner diameter	15.80mm
Material	Steel
Surface protection	Other
Sheathing material 1st coating	PVC
Operating temperature	-40-+80°C
Colour	Black
Bending strength	Flexible

Packaging

Outer Quantity	1000
Outer Dimensions (inches)	20x30x30
Weight Uom	0.33 lbs. Each

Documents / Support Tools

Technical Drawing / Data Sheet	TDS000010
Technical Drawing / Data Sheet	TDS000117
Catalog US	Available on Website