



Catalog Number: LTZUS07B-C
Product ID: 7TAA012LT0R0016
UPC Number: 78621011630
EAN Number: 05415022394672
Status: A



Liquid Tight Flexible Metallic Conduit, Galvanised Steel Core with PVC Jacket, Conduit Size 2 Inch, Length 30 Meters/100 Feet, Halogen Free, UL 360, CSA, Compliant to RoHS, Working Temperature -40 to 80 Degrees C, Black

Representative

North American Specifications (UNSPSC)

UNSPSC	39131706 Electrical conduit
IGCC	5543 Liquid Tight Conduit
Type	Liquid Tight Flexible Metallic Conduit
Standard	UL 360, CSA, RoHS
Trade Size	2 in ; 63 mm
Outside Diameter	2.375 in
Inside Diameter	2.020 in
Length	100 ft ; 30 m
Material	Galvanized Steel Core
Finish	PVC Jacket
Color	Black

European Specifications (ETIM)

ETIM	EC001179 Protective metallic hose
Nominal diameter	63mm
Nominal size in inch	2 inch
Outer diameter	60.33mm
Inner diameter	51.31mm
Material	Steel
Surface protection	Other
Sheathing material 1st coating	PVC
Operating temperature	-40-+80°C
Colour	Black
Bending strength	Flexible

Packaging

Outer Quantity	100
Outer Dimensions (inches)	32x32x20
Weight Uom	1.45 lbs. Each

Documents / Support Tools

Technical Drawing / Data Sheet	TDS000010
Technical Drawing / Data Sheet	TDS000117
Catalog US	Available on Website