



**Catalog Number:** LTZUS09B-A  
**Product ID:** 7TAA012LT0R0008  
**UPC Number:** 78621011621  
**EAN Number:** 05415022394597  
**Status:** A



Liquid Tight Flexible Metallic Conduit, Galvanised Steel Core with PVC Jacket, Conduit Size 3 Inch, Length 8 Meters/25 Feet, Halogen Free, UL 360, CSA, Compliant to RoHS, Working Temperature -40 to 80 Degrees C, Black

Representative

#### North American Specifications (UNSPSC)

UNSPSC	39131706 Electrical conduit
IGCC	5543 Liquid Tight Conduit
Type	Liquid Tight Flexible Metallic Conduit
Standard	UL 360, CSA, RoHS
Trade Size	3 in ; 80 mm
Outside Diameter	3.500 in
Inside Diameter	3.070 in
Length	25 ft ; 8 m
Material	Galvanized Steel Core
Finish	PVC Jacket
Color	Black

#### European Specifications (ETIM)

ETIM	EC001179 Protective metallic hose
Nominal diameter	80mm
Nominal size in inch	3 inch
Outer diameter	88.90mm
Inner diameter	77.98mm
Material	Steel
Surface protection	Other
Sheathing material 1st coating	PVC
Operating temperature	-40-+80°C
Colour	Black
Bending strength	Flexible

#### Packaging

Outer Quantity	25
Outer Dimensions (inches)	6.5x60.25x60.25
Weight Uom	2.52 lbs. Each

#### Documents / Support Tools

Technical Drawing / Data Sheet	TDS000010
Technical Drawing / Data Sheet	TDS000117
Catalog US	Available on Website