



Representative

Catalog Number: NCG-0503G
Product ID: 7TCA303070R0194
UPC Number: 78621015338
EAN Number: 05415022425116
Status: A

Non Armoured Cable Gland, Thread Size 1/2 Inch NPT, Cable Range 10 to 14mm, Thread Length 11mm, Nylon, Grey

- Low profile compact cable glands
- Wide cable clamping range
- Good corrosion resistance

North American Specifications (UNSPSC)

UNSPSC	39121431 Cable gland connector
IGCC	4601 Cable gland connector
Type	Non Armoured Cable Gland
Application	General purpose, Panel building, Light fixture and housings
Standard	UL514B, CSA, RoHS, WEEE, LVD
Size	1/2 Inch NPT
Conductor Range	10 to 14 Millimeters
Material	Nylon
Color	Gray
NEMA Rating	4
Temperature Rating	-20 to +100 C

European Specifications (ETIM)

ETIM	EC000441 Cable screw gland
Thread type	NPT
Nominal thread size inch/gas pipe thread	1/2 inch
Thread length	11mm
Suitable for cable diameter	10 - 14mm
Material	Plastic
Material quality	Polyamide (PA)
Halogen free	Y
Degree of protection (IP)	IP68
Colour	Dark grey
Model	Straight
Operating temperature	-20-+100°C

Packaging

Inner Quantity	10
Inner Dimensions (inches)	7.09x3.54x3.54
Outer Quantity	50
Outer Dimensions (inches)	3.94x15.75x11.02
Weight Uom	0.01 lbs. Each

Documents / Support Tools

Technical Drawing / Data Sheet	TDS000030
Instruction Sheet	TA05283-TB2
Support/Tools	Available on Website

Header

3D Model	Available on Website
----------	----------------------

