



Actual

**Catalog Number:** NCG-0751B  
**Product ID:** 7TCA303070R0031  
**UPC Number:** 78621015215  
**EAN Number:** 05415022423969  
**Status:** A

Non Armoured Cable Gland, Thread Size 3/4 Inch NPT, Cable Range 9 to 16 Millimeters, Thread Length 15 Millimeters, Nylon, Black

- Low profile compact cable glands
- Wide cable clamping range
- Good corrosion resistance

### North American Specifications (UNSPSC)

UNSPSC	39121431 Cable gland connector
IGCC	4601 Cable gland connector
Brand Name	ABB
Type	Non Armoured Cable Gland
Application	General purpose, Panel building, Light fixture and housings
Standard	UL514B, CSA, RoHS, WEEE, LVD
Size	3/4 Inch NPT
Conductor Range	9 to 16 Millimeters
Material	Nylon
Color	Black
NEMA Rating	4
Temperature Rating	-20 to +100 C

### European Specifications (ETIM)

ETIM	EC000441 Cable screw gland
Thread type	NPT
Nominal thread size inch/gas pipe thread	3/4 inch
Thread length	15mm
Suitable for cable diameter	9 - 16mm
Material	Plastic
Material quality	Polyamide (PA)
Halogen free	Y
Degree of protection (IP)	IP68
Colour	Black
Model	Straight
Operating temperature	-20-+100°C

### Packaging

Inner Quantity	5
Inner Dimensions (inches)	7.09x3.54x3.54
Outer Quantity	20
Outer Dimensions (inches)	3.94x15.75x11.02
Weight Uom	0.01 lbs. Each

### Documents / Support Tools

Technical Drawing / Data Sheet	TDS000030
Instruction Sheet	TA05283-TB2
Support/Tools	Available on Website

### Header

3D Model	Available on Website
----------	----------------------

