



Representative

**Catalog Number:** NCG-M202LG  
**Product ID:** 7TCA303070R0087  
**UPC Number:** 78621015245  
**EAN Number:** 05415022424256  
**Status:** Active

Non Armoured Cable Gland, Thread Size M20, Cable Range 6 to 12 Millimeters, Thread Length 10 Millimeters, Nylon, Light Grey

- Low profile compact cable glands
- Wide cable clamping range
- Good corrosion resistance

### North American Specifications (UNSPSC)

UNSPSC	39121431 Cable gland connector
IGCC	4601 Cable gland connector
Brand Name	T&B
Type	Non Armoured Cable Gland
Application	General purpose, Panel building, Light fixture and housings
Standard	UL514B, CSA, RoHS, WEEE, LVD
Size	M20
Conductor Range	6 to 12 Millimeters
Material	Nylon
Color	Light Gray
NEMA Rating	NEMA 4
Temperature Rating	-20 to +100 Degrees C

### European Specifications (ETIM)

ETIM	EC000441 Cable screw gland
Thread type	Metric
Nominal thread size metric/PG	20
Pitch thread	1.5mm
Thread length	10mm
Suitable for cable diameter	6 - 12mm
Material	Plastic
Material quality	Polyamide (PA)
Halogen free	Y
Degree of protection (IP)	IP68
Colour	Light grey
Model	Straight
Operating temperature	-20-+100°C

### Packaging

Inner Quantity	10
Inner Dimensions (inches)	7.09x3.54x3.54
Outer Quantity	50
Outer Dimensions (inches)	3.94x15.75x11.02
Weight Uom	0.01 lbs. Each

### Documents / Support Tools

Technical Drawing / Data Sheet	TDS000030
Technical Drawing / Data Sheet Canada	TDS000030
Instruction Sheet	TA05283-TB2
Support/Tools	Available on Website
Video US	Available on Website

Thomas & Betts - USA