



Representative

Catalog Number: NCG-M252LG
Product ID: 7TCA303070R0093
UPC Number: 78621015251
EAN Number: 05415022424317
Status: Active

Non Armoured Cable Gland, Thread Size M25, Cable Range 11 to 17 Millimeters, Thread Length 8 Millimeters, Nylon, Light Grey

- Low profile compact cable glands
- Wide cable clamping range
- Good corrosion resistance

North American Specifications (UNSPSC)

UNSPSC	39121431 Cable gland connector
IGCC	4601 Cable gland connector
Brand Name	T&B
Type	Non Armoured Cable Gland
Application	General purpose, Panel building, Light fixture and housings
Standard	UL514B, CSA, RoHS, WEEE, LVD
Size	M25
Conductor Range	11 to 17 Millimeters
Material	Nylon
Color	Light Gray
NEMA Rating	NEMA 4
Temperature Rating	-20 to +100 Degrees C

European Specifications (ETIM)

ETIM	EC000441 Cable screw gland
Thread type	Metric
Nominal thread size metric/PG	25
Pitch thread	1.5mm
Thread length	8mm
Suitable for cable diameter	11 - 17mm
Material	Plastic
Material quality	Polyamide (PA)
Halogen free	Y
Degree of protection (IP)	IP68
Colour	Light grey
Model	Straight
Operating temperature	-20-+100°C

Packaging

Inner Quantity	10
Inner Dimensions (inches)	7.09x3.54x3.54
Outer Quantity	40
Outer Dimensions (inches)	3.94x15.75x11.02
Weight Uom	0.04 lbs. Each

Documents / Support Tools

Technical Drawing / Data Sheet	TDS000030
Technical Drawing / Data Sheet Canada	TDS000030
Instruction Sheet	TA05283-TB2
Support/Tools	Available on Website
Video US	Available on Website

Thomas & Betts - USA