



Actual

Catalog Number: NCG-M751B
Product ID: 7TCA303070R0032
UPC Number: 78621015203
EAN Number: 05415022423884
Status: A

Non Armoured Cable Gland, Thread Size M75, Cable Range 48 to 55mm, Thread Length 25mm, Nylon, Black

- Low profile compact cable glands
- Wide cable clamping range
- Good corrosion resistance

North American Specifications (UNSPSC)

UNSPSC	39121431 Cable gland connector
IGCC	4601 Cable gland connector
Type	Non Armoured Cable Gland
Application	General purpose, Panel building, Light fixture and housings
Standard	UL514B, CSA, RoHS, WEEE, LVD
Size	M75
Conductor Range	48 to 55 Millimeters
Material	Nylon
Color	Black
NEMA Rating	4
Temperature Rating	-20 to +100 C

European Specifications (ETIM)

ETIM	EC000441 Cable screw gland
Thread type	Metric
Nominal thread size metric/PG	75
Pitch thread	1.5mm
Thread length	25mm
Suitable for cable diameter	48 - 55mm
Material	Plastic
Material quality	Polyamide (PA)
Halogen free	Y
Degree of protection (IP)	IP68
Colour	Black
Model	Straight
Operating temperature	-20-+100°C

Packaging

Inner Quantity	4
Inner Dimensions (inches)	7.09x3.54x3.54
Outer Quantity	24
Outer Dimensions (inches)	3.94x15.75x11.02
Weight Uom	0.01 lbs. Each

Documents / Support Tools

Technical Drawing / Data Sheet	TDS000030
Instruction Sheet	TA05283-TB2
Support/Tools	Available on Website

Header

3D Model	Available on Website
----------	----------------------

