



Representative

**Catalog Number:** NCG-PG481LG  
**Product ID:** 7TCA303070R0149  
**UPC Number:** 78621015291  
**EAN Number:** 05415022424683  
**Status:** Active

Non Armoured Cable Gland, Thread Size PG48, Cable Range 34 to 44 Millimeters, Thread Length 14 Millimeters, Nylon, Light Grey

- Low profile compact cable glands
- Wide cable clamping range
- Good corrosion resistance

### North American Specifications (UNSPSC)

UNSPSC	39121431 Cable gland connector
IGCC	4601 Cable gland connector
Brand Name	T&B
Type	Non Armoured Cable Gland
Application	General purpose, Panel building, Light fixture and housings
Standard	UL514B, CSA, RoHS, WEEE, LVD
Size	PG48
Conductor Range	34 to 44 Millimeters
Material	Nylon
Color	Light Gray
NEMA Rating	NEMA 4
Temperature Rating	-20 to +100 Degrees C

### European Specifications (ETIM)

ETIM	EC000441 Cable screw gland
Thread type	PG
Nominal thread size metric/PG	48
Thread length	14mm
Suitable for cable diameter	34 - 44mm
Material	Plastic
Material quality	Polyamide (PA)
Halogen free	Y
Degree of protection (IP)	IP68
Colour	Light grey
Model	Straight
Operating temperature	-20-+100°C

### Packaging

Inner Quantity	5
Inner Dimensions (inches)	7.09x3.54x3.54
Outer Quantity	5
Outer Dimensions (inches)	3.94x15.75x11.02
Weight Uom	0.01 lbs. Each

### Documents / Support Tools

Technical Drawing / Data Sheet	TDS000030
Technical Drawing / Data Sheet Canada	TDS000030
Instruction Sheet	TA05283-TB2
Support/Tools	Available on Website
Video US	Available on Website

Thomas & Betts - USA