



Actual



Family



Representative

Catalog Number: NPG-M321LG
Product ID: 7TCA303070R0014
UPC Number: 78621013808
EAN Number: 05415022403381
Status: Active

Quick Connect Cable Gland, Thread Size M32, Cable Range 15 to 21 Millimeters, Thread Length 9 Millimeters, Nylon, Light Grey

- Single Piece (No locknut required)
- Fast and simple to install
- Low internal profile
- Corrosion resistant

North American Specifications (UNSPSC)

UNSPSC	39121431 Cable gland connector
IGCC	4601 Cable gland connector
Brand Name	T&B
Type	Quick Connect Cable Gland
Application	General purpose, Ideal for Panel building and Volume Installers
Standard	cULus, RoHS, WEEE, LVD
Size	M32
Conductor Range	15 to 21 Millimeters
Material	Nylon
Color	Light Gray
Temperature Rating	-20 to +100 Degrees C

European Specifications (ETIM)

ETIM	EC000441 Cable screw gland
Thread type	Metric
Nominal thread size metric/PG	32
Pitch thread	1.5mm
Thread length	9mm
Suitable for cable diameter	15 - 21mm
Material	Plastic
Material quality	Polyamide (PA)
Halogen free	Y
Degree of protection (IP)	IP68
Colour	Light grey
Model	Straight
Operating temperature	-20-+100°C

Packaging

Inner Quantity	5
Inner Dimensions (inches)	7.09x3.54x3.54
Outer Quantity	20
Outer Dimensions (inches)	3.94x15.75x11.02
Weight Uom	0.01 lbs. Each

Documents / Support Tools

Technical Drawing / Data Sheet US	TDS000036
Technical Drawing / Data Sheet Canada	TDS000036
Instruction Sheet	TA05285-TB2
Support/Tools	Available on Website

Thomas & Betts - USA