



Actual

**Catalog Number:** PPCOF-29B.50  
**Product ID:** 7TAA292730R0020  
**UPC Number:** 78620999813  
**EAN Number:** 07630030264603  
**Status:** A

Divisible Flexible Black Conduit, (PPCOF) Material - Polypropylene, Conduit Size NW - 29, 50 Meters

- Can be opened and closed again in longitudinal directional any time
- PMA standard nominal widths can be used in combination with all PMA fittings
- Easy installation
- Trouble-free retrofitting
- Self-extinguishing
- Applicable also for repairs
- Vehicle Building

#### North American Specifications (UNSPSC)

UNSPSC	39131706 Electrical conduit
IGCC	5535 Electrical conduit
Type	Divisible Conduit
Application	Machine
Trade Size	NW29
Length	50 m
Flexibility	Medium
Material	Polypropylene
Color	Black

#### European Specifications (ETIM)

ETIM	EC001175 Corrugated plastic hose
Nominal diameter	32mm
Outer diameter	34.5mm
Inner diameter	26.6mm
Material	Polypropylene
Compressive strength	180N
Operating temperature	-20 - +105°C
Fire resistance in accordance with UL94	V2
UV resistant	Y
Colour	Black
Sheathing material	Not sheathed
Bending strength	Flexible
Lengthwise slotted	N
Closable (two-part)	Y
Approved according to DIN EN 61386-23	N
Approved according to UR	N
Approved according to CSA	N
Approved according to LUL/British Standard	N
Approved according to Lloyd's Register TA	N
Approved according to UTAC	N
Approved according to DIN 5510	N
Approved according to NF F 16-101	N

#### Packaging



Inner Quantity	1
Outer Quantity	5
Outer Dimensions (inches)	47.244x31.496x30.709
Weight Uom	19.68 lbs. Each