



Actual

Catalog Number: RNCG-M404
Product ID: 7TCA303080R0029
UPC Number: 78621012008
EAN Number: 05415022396072
Status: A

Non Armoured Cable Gland for Rail, Thread Size M40, Cable Range 22 to 32 Millimeters, Thread Length 18 Millimeters, Nylon

- EN45545-2 Compliant HL3 for R22 and R23 usage
- Lightweight nylon construction
- Large capacity sealing range
- Corrosion resistant
- R22 interior locations for small components
- R23 exterior locations for small components

North American Specifications (UNSPSC)

UNSPSC	39121431 Cable gland connector
IGCC	4601 Cable gland connector
Brand Name	ABB
Type	Non Armoured Cable Gland for Rail
Application	General purpose rolling stock and infrastructure applications
Standard	RoHS, WEEE, LVD
Size	M40
Conductor Range	22 to 32 Millimeters
Material	Nylon
Color	Light Gray
Temperature Rating	-40 to +100 Degrees C
Environmental Conditions	Fire EN 45545-2 HL3

European Specifications (ETIM)

ETIM	EC000441 Cable screw gland
Thread type	Metric
Nominal thread size metric/PG	40
Pitch thread	1.5mm
Thread length	18mm
Suitable for cable diameter	22 - 32mm
Material	Plastic
Material quality	Polyamide (PA)
Halogen free	Y
Degree of protection (IP)	IP68
Colour	Light grey
Model	Straight
Operating temperature	-40-+100°C

Packaging

Inner Quantity	5
Outer Quantity	5
Outer Dimensions (inches)	7.09x3.54x3.54
Weight Uom	0.1 lbs. Each

Documents / Support Tools

Technical Drawing / Data Sheet	TDS000025
Instruction Sheet	TA05283-TB2
Support/Tools	Available on Website

