



Actual

Catalog Number: S2000PWL-0
Product ID: 7TAG009740R0008
UPC Number: 78621091397
EAN Number: 05414363129974
Status: A

Polyethylene Terephthalate (P.E.T.) Hook and Loop Wraparound Sleeving, Black, Nominal I.D. of 50.80mm (2.0 Inches), Nominal Diameter Range of 38.10mm (1.50 Inches) to 88.90mm (3.50 Inches), 15.24m (50 Foot) Mini Spool

- Braided wire protection sleeving is used to bundle and protect wires and cables from abrasion and excessive wear.
- The sleeving is resistant to chemicals, fungus, fuels, UV sunlight, and has an indefinite shelf life.
- It is easily cut with a hot knife, which seals the end preventing frayings. Ends can also be secured using Ty-Rap cable ties.
- Application Tools: WTBM

North American Specifications (UNSPSC)

UNSPSC	39131602 Expandable braided sleeving
IGCC	5392 Expandable braided sleeving
Type	Braided Sleeve
Special Features	Braided wire protection sleeving is used to bundle and protect wires and cables from abrasion and excessive wear.
Color	Black
Length	50 ft
Temperature Rating	-94 to 257 F ; -70 C to 125 C
Melt Point	230 C
Material	PET (Polyethylene Terephthalate)

European Specifications (ETIM)

ETIM	EC001937 Cable protection for installation duct
Material	Plastic
Material quality	Other
Halogen free	Y
Construction type	Protective strip
Length	15240mm
Colour	Black

Packaging

Outer Quantity	1
Weight Uom	5.63 lbs. Each

Documents / Support Tools

Technical Drawing / Data Sheet US	Available on Website
Safety Data Sheet (SDS) Global	SDS-00046-TB2