



Actual

**Catalog Number:** SCG-0502  
**Product ID:** 7TCA303040R0056  
**UPC Number:** 78621015886  
**EAN Number:** 05415022429916  
**Status:** A

Non Armoured Cable Gland, Thread Size 1/2 Inch NPT, Cable Range 6 to 12mm, Thread Length 13mm, Stainless Steel

- Low profile compact cable glands
- Wide cable clamping range
- Excellent corrosion resistance
- Ideal for wet locations

**North American Specifications (UNSPSC)**

UNSPSC	39121431 Cable gland connector
IGCC	4601 Cable gland connector
Type	Non Armoured Cable Gland
Application	General purpose, Panel building, Light fixture and housings
Standard	cULus, RoHS, WEEE, LVD
Size	1/2 Inch NPT
Conductor Range	6 to 12 Millimeters
Material	316 Stainless Steel
Color	Metallic
NEMA Rating	4
Temperature Rating	-20 to +100 C

**European Specifications (ETIM)**

ETIM	EC000441 Cable screw gland
Thread type	NPT
Nominal thread size inch/gas pipe thread	1/2 inch
Thread length	13mm
Suitable for cable diameter	6 - 12mm
Material	Metal
Material quality	Stainless steel V4A
Surface protection	Untreated
Degree of protection (IP)	IP68
Colour	Natural colour
Model	Straight
Operating temperature	-20-+100°C

**Packaging**

Inner Quantity	10
Inner Dimensions (inches)	7.09x3.54x3.54
Outer Quantity	50
Outer Dimensions (inches)	3.94x15.75x11.02
Weight Uom	9.1 lbs. per 100

**Documents / Support Tools**

Technical Drawing / Data Sheet	TDS000032
Instruction Sheet	TA05283-TB2
Support/Tools	Available on Website

