



Actual

**Catalog Number:** SCG-M201  
**Product ID:** 7TCA303040R0009  
**UPC Number:** 78621015837  
**EAN Number:** 05415022429442  
**Status:** Active

Non Armoured Cable Gland, Thread Size M20, Cable Range 5 to 9 Millimeters, Thread Length 8 Millimeters, Stainless Steel

- Low profile compact cable glands
- Wide cable clamping range
- Excellent corrosion resistance
- Ideal for wet locations

### North American Specifications (UNSPSC)

UNSPSC	39121431 Cable gland connector
IGCC	4601 Cable gland connector
Brand Name	T&B
Type	Non Armoured Cable Gland
Application	General purpose, Panel building, Light fixture and housings
Standard	cULus, RoHS, WEEE, LVD
Size	M20
Conductor Range	5 to 9 Millimeters
Material	316 Stainless Steel
Color	Metallic
NEMA Rating	NEMA 4
Temperature Rating	-20 to +100 Degrees C

### European Specifications (ETIM)

ETIM	EC000441 Cable screw gland
Thread type	Metric
Nominal thread size metric/PG	20
Pitch thread	1.5mm
Thread length	8mm
Suitable for cable diameter	5 - 9mm
Material	Metal
Material quality	Stainless steel V4A
Surface protection	Untreated
Degree of protection (IP)	IP68
Colour	Natural colour
Model	Straight
Operating temperature	-20-+100°C

### Packaging

Inner Quantity	10
Inner Dimensions (inches)	7.09x3.54x3.54
Outer Quantity	50
Outer Dimensions (inches)	3.94x15.75x11.02
Weight Uom	0.02 lbs. Each

### Documents / Support Tools

Technical Drawing / Data Sheet	TDS000032
Technical Drawing / Data Sheet Canada	TDS000032
Instruction Sheet	TA05283-TB2
Support/Tools	Available on Website

Thomas & Betts - USA