



Actual

Catalog Number: SCG-M325-L
Product ID: 7TCA303040R0030
UPC Number: 78621015859
EAN Number: 05415022429657
Status: Active

Non Armoured Cable Gland, Thread Size M32, Cable Range 18 to 25 Millimeters, Thread Length 15 Millimeters, Stainless Steel

- Low profile compact cable glands
- Wide cable clamping range
- Excellent corrosion resistance
- Ideal for wet locations

North American Specifications (UNSPSC)

UNSPSC	39121431 Cable gland connector
IGCC	4601 Cable gland connector
Brand Name	T&B
Type	Non Armoured Cable Gland
Application	General purpose, Panel building, Light fixture and housings
Standard	cULus, RoHS, WEEE, LVD
Size	M32
Conductor Range	18 to 25 Millimeters
Material	316 Stainless Steel
Color	Metallic
NEMA Rating	NEMA 4
Temperature Rating	-20 to +100 Degrees C

European Specifications (ETIM)

ETIM	EC000441 Cable screw gland
Thread type	Metric
Nominal thread size metric/PG	32
Pitch thread	1.5mm
Thread length	15mm
Suitable for cable diameter	18 - 25mm
Material	Metal
Material quality	Stainless steel V4A
Surface protection	Untreated
Degree of protection (IP)	IP68
Colour	Natural colour
Model	Straight
Operating temperature	-20-+100°C

Packaging

Inner Quantity	10
Inner Dimensions (inches)	7.09x3.54x3.54
Outer Quantity	10
Outer Dimensions (inches)	3.94x15.75x11.02
Weight Uom	0.02 lbs. Each

Documents / Support Tools

Technical Drawing / Data Sheet	TDS000032
Technical Drawing / Data Sheet Canada	TDS000032
Instruction Sheet	TA05283-TB2
Support/Tools	Available on Website

Thomas & Betts - USA